

# 60mm Travel, High Vacuum ( $10^{-6}$ Torr) Motorized Rotary Stage, Integrated Controller

See More by [Zaber™](#)



Stock #74-704 NEW **1 In Stock**

MRP ₹5,91,215

Price inclusive of all taxes

ADD TO CART

### Volume Pricing

Qty 1+	₹5,91,215 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric **Type:**

No **Encoder:**

No **Manual Control/ LED Indicators:**

Zaber Technologies Inc. **Manufacturer:**

X-RSW60A-SV2T9 **Model Number:**

Requires Accessory Kit, [#75-301](#), for operation. **Note:**

2-Phase Stepper **Type of Motor:**

### Physical & Mechanical Properties

Rotary	<b>Type of Movement:</b>
131.5 x 73.2	<b>Stage Size (mm):</b>
360	<b>Travel (°):</b>
0.14	<b>Accuracy (°):</b>
<0.04	<b>Backlash (°):</b>
31.7	<b>Height (mm):</b>
20	<b>Load Capacity (kg):</b>
200	<b>Load Capacity (N):</b>
<0.02	<b>Repeatability (°):</b>
<0.349	<b>Resolution (µrad):</b>
0.000143 - 100	<b>Speed (°/s):</b>
0.72	<b>Weight (kg):</b>
60	<b>Table Diameter (mm):</b>
100	<b>Max. Continuous Torque (N·cm):</b>

## Electrical

950	<b>Current (mA):</b>
950	<b>Maximum Operating Current (mA):</b>

## Hardware & Interface Connectivity

Precision Worm Gear	<b>Type of Drive:</b>
24-48 VDC; Power Supply w/US Plug found in accessories kit, <a href="#">#75-301</a>	<b>Power Supply:</b>
RS-232, USB	<b>Computer Interface:</b>

## Material Properties

High vacuum (10 <sup>-6</sup> Torr)	<b>Vacuum Compatibility:</b>
-------------------------------------	------------------------------

## Environmental & Durability Factors

0 to +50	<b>Operating Temperature (°C):</b>
----------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>
Canada	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- High Resolution with 360° Continuous Rotation
- Integrated Motor and Controller
- Vacuum-Compatible Options
- Controlled Manually or via RS-232 Serial Interface
- Power Supply and Data Cable Sold as Separate Accessories

- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ Motorized Rotary Stage Systems are designed to hold 1" or 25mm optical components on both the top and bottom plates, and provide precise, 360° rotation. The compact bearing design can handle up to 45 lb (20kg) loads while providing 4.1µrad resolution rotational movement. Encoder versions are available for all travel lengths, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ Motorized Rotary Stage Systems also includes a potentiometer located on the back of the stage to provide a convenient way to manually control position.

**Note:** A 24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories. These stages utilize the same accessories as the [Zaber™ High Precision Motorized Stage System](#).

## Technical Information

**Device Overview / Connectors**

Images are shown looking into the device.

**Power**

Pin	Description
1	24 - 48 V
2	GND (Note: power supplies ground this pin to AC Earth)

**Note:** To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.

