

[See all 6 Products in Family](#)

# 60mm Travel, Ultra Precision Linear Motor Stage, Integrated Controller, Linear Encoder

See More by [Zaber™](#)



Stock **#70-563** 1 In Stock

-

1

+

₹8,75,088

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹8,75,088 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                 |                                 |
|-------------------------|---------------------------------|
| Metric                  | Type:                           |
| Yes                     | Encoder:                        |
| Yes                     | Manual Control/ LED Indicators: |
| Zaber Technologies Inc. | Manufacturer:                   |
| Note:                   |                                 |

|                                                                                                                                                                                                                                                                                                  |                                 |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|
| Requires a 24-48 VDC power supply and either <a href="#">#15-295</a> for USB connectivity or <a href="#">#15-297</a> for RS-232 connectivity. A data cable ( <a href="#">#15-296</a> or <a href="#">#15-299</a> ) can be used to daisy chain multiple stages together to control simultaneously. |                                 |
| Moving Magnet Track Linear Mtor                                                                                                                                                                                                                                                                  | Type of Motor:                  |
| Linear Analog Encoder                                                                                                                                                                                                                                                                            | Encoder Type:                   |
| Physical & Mechanical Properties                                                                                                                                                                                                                                                                 |                                 |
| Linear (X)                                                                                                                                                                                                                                                                                       | Type of Movement:               |
| Crossed-Roller Bearing                                                                                                                                                                                                                                                                           | Guide System:                   |
| 190 x 151.5                                                                                                                                                                                                                                                                                      | Stage Size (mm):                |
| 60                                                                                                                                                                                                                                                                                               | Travel (mm):                    |
| 1                                                                                                                                                                                                                                                                                                | Accuracy (µm):                  |
| 44                                                                                                                                                                                                                                                                                               | Height (mm):                    |
| 12                                                                                                                                                                                                                                                                                               | Load Capacity (kg):             |
| <0.08                                                                                                                                                                                                                                                                                            | Repeatability (µm):             |
| 0.00061 - 1200                                                                                                                                                                                                                                                                                   | Speed (mm/s):                   |
| 3.76                                                                                                                                                                                                                                                                                             | Weight (kg):                    |
| Electrical                                                                                                                                                                                                                                                                                       |                                 |
| 3000                                                                                                                                                                                                                                                                                             | Maximum Operating Current (mA): |
| Hardware & Interface Connectivity                                                                                                                                                                                                                                                                |                                 |
| Moving Magnet Track Linear Mtor                                                                                                                                                                                                                                                                  | Type of Drive:                  |
| Power Supply Required and Sold Separately.<br>USA: <a href="#">#70-960</a><br>Europe: <a href="#">#70-960</a><br>Japan: <a href="#">#23-662</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#70-960</a>                                                                              | Power Supply:                   |
| RS-232                                                                                                                                                                                                                                                                                           | Computer Interface:             |
| Environmental & Durability Factors                                                                                                                                                                                                                                                               |                                 |
| 10 - 40                                                                                                                                                                                                                                                                                          | Operating Temperature (°C):     |
| Regulatory Compliance                                                                                                                                                                                                                                                                            |                                 |
| <a href="#">Compliant</a>                                                                                                                                                                                                                                                                        | RoHS 2015:                      |
| <a href="#">View</a>                                                                                                                                                                                                                                                                             | Certificate of Conformance:     |
| <a href="#">Compliant</a>                                                                                                                                                                                                                                                                        | Reach 247:                      |
| Canada                                                                                                                                                                                                                                                                                           | Country of Origin:              |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000                                                                                          | Imported By:                    |

## Product Details

- 60, 110, 210mm Travel Options
- Up to 1200mm/s Speed
- Ultra-High Repeatability and Accuracy

Zaber™ Ultra High Precision Linear Motorized Stages are computer-controlled linear stages that utilize a moving magnet track linear motor and centrally located encoder to accurately and precisely position optical components or subsystems. These stages can connect directly to a computer's USB or RS-232 port and are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#) for quick set up and intuitive automation and control. The linear analog encoder has 1nm count size ensuring 1µm positional accuracy, < 0.08µm repeatability, and consistent minimal incremental movement steps down to 20nm. Zaber™ Ultra High Precision Linear Motorized Stages are driven by non-cogging ironless linear motors which allow for speeds up to 1200mm/s with a minimum speed and speed resolution of 0.61mm/s. These stages are designed with metric tapped holes for mounting and an indexed knob and push switch for manual control when needed.

