

TECHSPEC® 6.25mm Dia. x 10mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-208** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹5,481.00

ADD TO CART

Qty 1-5

₹5,481.00

Qty 6+

₹4,394.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):

10.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 7.83
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <3
Center Thickness CT (mm): 4.09 ±0.10
Center Thickness CT 1 (mm): 3.06 ±0.05
Center Thickness CT 2 (mm): 1.03 ±0.05
Radius R ₁ (mm): 6.98
Radius R ₂ (mm): -4.35
Radius R ₃ (mm): -41.01
Edge Thickness ET (mm): 3.23
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View