

[See all 2 Products in Family](#)

## 62 x 147mm FL, Grade 1, Double-Convex Lens



Stock #31-795 CLEARANCE **20+ In Stock**

1  MRP ₹530

 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹530 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

62.00 **Diameter (mm):**

### Optical Properties

147.00 **Effective Focal Length EFL (mm):**

### Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

United States

**Country of Origin:**

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

50mm and Larger Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

