

**TECHSPEC® 6.25mm, Aluminum & VIS 0° Coated, N-BK7 Right Angle Prism**



N-BK7 Right Angle Prisms

Stock **#48-547** **20+ In Stock**

1  MRP ₹8,828

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹8,828 each
Qty 6-25	₹7,062 each
Qty 26-49	₹6,608 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Right Angle Prism **Type:**

**Physical & Mechanical Properties**

±0.1 **Dimensional Tolerance (mm):**

**Bevel:**

Protective as needed

8.80 Length of Hypotenuse (mm):

6.25 Length of Legs (mm):

## Optical Properties

Coating:

VIS 0° & Aluminized

Substrate:

N-BK7

Surface Quality:

60-40

Angle Tolerance (arcmin):

±2

Image Orientation:

Left-Handed

Coating Specification:

Hypotenuse:  $R_{avg} > 85\%$  @ 400 - 700nm

Legs:  $R_{avg} \leq 0.4\%$  @ 425 - 675nm

Ray Deviation (°):

90

Wavelength Range (nm):

425 - 675

Damage Threshold, By Design:

Hypotenuse:  $0.3 \text{ J/cm}^2$  @ 532nm & 1064nm, 10ns

Legs:  $5 \text{ J/cm}^2$  @ 532nm, 10ns

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.50

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

Singapore

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ray Deviation of 90°
- Left Handed Image
- Available with Aluminized and AR Coated Faces
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® N-BK7 Right Angle Prisms are made from precision N-BK7 for use in a variety of visible light applications. Right angle prisms are generally used to bend image paths or redirect light at 90°. This produces a left-handed image, and depending on the orientation of the prism, the image may be inverted or reverted. TECHSPEC® N-BK7 Right Angle Prisms can also be used in combination for image/beam displacement. These right-angle prisms are additionally offered with aluminized and AR Coated surfaces.

## Technical Information



Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

