

TECHSPEC® 6.25mm Dia. x 25mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock **#84-330** 10 TO 12 DAYS

- 1 + **₹9,131.00**

ADD TO CART

Qty 1+
₹9,131.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00

Focal Length Tolerance (%):
±1

Back Focal Length BFL (mm):

23.38
Focal Length Specification Wavelength (nm): 405.00
Clear Aperture CA (mm): 5.25
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Center Thickness CT 1 (mm): 2.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 13.57
Radius R₂ (mm): -13.57
Radius R₃ (mm): -43.89
Edge Thickness ET (mm): 2.52
Substrate: ☐ N-FK5 / F2H1
Surface Quality: 40-20
f/#: 4
Numerical Aperture NA: 0.13
Coating: UV-VIS (345-700nm)
Coating Specification: R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 345 - 700

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Compliant