

TECHSPEC® 6.25mm, UV Enhanced Aluminum, N-BK7 Right Angle Prism Mirror (Leg Coated)



Stock #25-706 **3 In Stock**

MRP ₹12,309

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹12,309 each
Qty 6-25	₹9,836 each
Qty 26-49	₹9,231 each
Need More?	Request Quote

Product Downloads

General

Right Angle Mirror **Type:**

Physical & Mechanical Properties

5.6 **Clear Aperture CA (mm):**

±0.1 **Dimensional Tolerance (mm):**

Protective as needed	Bevel:
90.00	Clear Aperture (%):
8.80	Length of Hypotenuse (mm):
6.25	Length of Legs (mm):

Optical Properties

Enhanced Aluminum (250-700nm)	Coating:
N-BK7	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
±2	Angle Tolerance (arcmin):
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
250 - 700	Wavelength Range (nm):
Metal	Coating Type:
0.5 J/cm ² @ 355nm, 10ns	Damage Threshold, Reference: <input type="checkbox"/>
1.25	Power (fringes) @ 632.8nm:
0.50	Irregularity (fringes) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Splits Input Image Into Two Paths Separated by 180°
- Variety of Sizes and Broadband Coatings Available
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® Right Angle Prism Mirrors (Leg Coated) are constructed from right angle prisms with a mirror coating on the two legs and an uncoated hypotenuse. The mirrored surfaces form a precise 90° angle, ideal for splitting an image from a single imaging lens onto two different cameras, or for combining two images onto a single camera.

Technical Information



Stock No.	Coating	A	B	C
#49-412	Enhanced Aluminum (450-650nm)	5mm	7.1mm	5mm
#65-847	Protected Gold (700-10000nm)			
#21-185	Protected Silver (450-10000nm)			
#47-004	Enhanced Aluminum (450-650nm)	10mm	14.1mm	10mm
#47-237	Protected Gold (700-10000nm)			
#21-186	Protected Silver (450-10000nm)			
#49-413	Enhanced Aluminum (450-650nm)	15mm	21.2mm	15mm
#65-848	Protected Gold (700-10000nm)			
#21-187	Protected Silver (450-10000nm)			
#49-414	Enhanced Aluminum (450-650nm)	20mm	28.3mm	20mm
#65-849	Protected Gold (700-10000nm)			
#21-188	Protected Silver (450-10000nm)			
#47-005	Enhanced Aluminum (450-650nm)	25mm	35.4mm	25mm
#47-238	Protected Gold (700-10000nm)			
#21-189	Protected Silver (450-10000nm)			
#47-006	Enhanced Aluminum (450-650nm)	50mm	70.7mm	50mm
#47-239	Protected Gold (700-10000nm)			
#21-190	Protected Silver (450-10000nm)			
#47-309	Enhanced Aluminum (450-650nm)	75mm	106.1mm	75mm
#47-310	Protected Gold (700-10000nm)			
#21-191	Protected Silver (450-10000nm)			

