

[See all 14 Products in Family](#)

632.8nm CWL, 0.50 FWHM, 25mm Dia. Ultra Narrow Filter



Stock **#21-386** **4 In Stock**

-

1

+

₹1,12,104

ADD TO CART

Volume Pricing	
Qty 1-5	₹1,12,104 each
Qty 6-25	₹1,00,816 each
Qty 26-49	₹95,756 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Filter Design: Two-Cavity	Note:

Physical & Mechanical Properties	
25.00 +0.00/-0.25	Diameter (mm):

21.00	Clear Aperture CA (mm):
6 +0.00/-0.25	Substrate Thickness (mm):
Optical Properties	
0	Angle of Incidence (°):
632.80	Center Wavelength CWL (nm):
0.50	Full Width-Half Max FWHM (nm):
Soda Lime Glass & Filter Glass	Substrate: ☐
>50	Minimum Transmission (%):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Bandwidths Between 0.2 and 5.0nm
- OD 4.0 Blocking Between 200 and 1200nm
- Rapid Custom Designs Available
- [Ultra Narrow Hard Coated Bandpass Filters](#) Also Available

Ultra Narrow Traditional Coated Bandpass Filters are ideal for use as laser line, laser cleanup, or laser excitation filters in demanding medical and laser applications. These filters provide OD 4 blocking by design, center wavelength tolerances as tight as 0.05nm, and bandwidths ranging from 0.2nm to 5.0nm. Multiple standard wavelength options including H-alpha hydrogen, HeNe laser, and Nd:YAG laser line are available. Rapid custom filters with bandwidth between 0.15 and 50nm and center wavelength between 340 and 2400nm are available. Please [contact us](#) for a quote.

Coating Curves

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).