


[See all 16 Products in Family](#)

632nm CWL, 6x6mm, OD8 High Blocking Bandpass Filter



6x6mm OD8 High Blocking Bandpass Filter

Stock **#26-722** **20+ In Stock**

MRP ₹20,078

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,078 each
Qty 6-25	₹16,042 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter **Type:**

qPCR **Typical Applications:**

Cy5 Excitation **Compatible Fluorophore:**

Physical & Mechanical Properties

6.0 x 6.0 +0.0/-0.25	Dimensions (mm):
≥5.4 Dia. (Centered)	Clear Aperture CA (mm):
2.00 (Nominal)	Thickness (mm):
Unmounted	Construction:
Painted opaque flat black	Edges:

Optical Properties

0 ±5	Angle of Incidence (°):
≥8.0	Optical Density OD (Average):
632.00 ±1.6	Center Wavelength CWL (nm):
18.00 (Nominal)	Full Width-Half Max FWHM (nm):
BOROFLOAT®	Substrate: <input type="checkbox"/>
≥95	Minimum Transmission (%):
Hard Coated	Coating:
60-40	Surface Quality:
350 - 850	Blocking Wavelength Range (nm):
5	Cone Half Angle (°):
±0.25	Wavelength Accuracy (%):

Environmental & Durability Factors

>100	Operating Temperature (°C):
ML-PRF-13830B	Durability:
Environmental Durability: ML-STD-810E, SECTION 507.3, PROCEDURE III - AGGRAVATED CYCLE, 10 CYCLES	
Coating Solubility and Cleaning: ML-C-48497A, IMMERSION IN ACETONE AND ALCOHOL	

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- OD ≥8 Blocking and >95% Minimum Peak Transmission in the Passband
- Designed for Common qPCR Fluorophores

- Excitation Filters and Emission Filters Available

OD8 Fluorescence Bandpass Filters deliver superior OD ≥ 8 blocking in their blocking band while offering high transmission in their transmission band. These hard-coated interference filters feature high-precision spectral consistency and enable industry leading signal-to-noise system performance and low crosstalk. They are available in black anodized aluminum mounts or unmounted in 6 x 6mm wafers for easy system integration. OD8 Fluorescence Bandpass Filters are ideal components in applications relying on fluorescence detection that require precision spectral clean-up, such as biomedical diagnostics instruments including DNA sequencers and polymerase chain reaction (PCR) analyzers. These filters are designed with passbands for the fluorescence excitation and emission of common qPCR fluorophores in mind, namely FAM, HEX, ROX and Cy5.


Technical Information

Overlay FAM Absorption & Emission with Excitation and Emission Filters




Overlay FAM Absorption & Emission with Excitation and Emission Filters

Overlay HEX Absorption & Emission with Excitation and Emission Filters




Overlay HEX Absorption and Emission with Excitation and Emission Filters

Overlay ROX Absorption & Emission with Excitation and Emission Filters



Overlay ROX Absorption and Emission with Excitation and Emission

Overlay Cy5 Absorption and Emission with Excitation and Emission Filters



Overlay Cy5 Absorption and Emission with Excitation and Emission Filters