

TECHSPEC[®] 632.8nm, 25mm Diameter, OD 4.0 Notch Filter



TECHSPEC OD 4.0 Notch Filters

Stock **#67-120** **6 In Stock**

[Additional Bandwidths](#)

-

1

+

₹33,476

ADD TO CART

Volume Pricing	
Qty 1-5	₹33,476 each
Qty 6-25	₹26,235 each
Qty 26-49	₹24,289 each
Need More?	Request Quote

Product Downloads

General

Type:	Notch Filter
-------	--------------

Physical & Mechanical Properties

Diameter (mm):	25.00 +0.00/-0.10
Clear Aperture CA (mm):	

21.3	
	Thickness (mm):
5.00 ±0.1	
	Construction:
Mounted in Black Anodized Ring	
	Physical Durability:
Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497ASection 4.5.4.2	
	Substrate Thickness (mm):
3.5 ±0.5	

Optical Properties	
	Optical Density OD (Average):
≥4.0	
	Center Wavelength CWL (nm):
632.80	
	Design Wavelength DWL (nm):
632.8	
	Full Width-Half Max FWHM (nm):
31.60	
	Coating:
Hard Coated	
	Surface Quality:
60-40	
	Transmission (%):
90	
	Transmission Wavelength (nm):
475 - 845	
	Reflection at CWL (%):
99	
	Transmitted Wavefront, RMS:
<1λ	

Threading & Mounting	
	Mount Thickness (mm):
5.0	

Environmental & Durability Factors	
	Environmental Durability:
Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- >OD 4.0 Rejection of Laser Wavelength from 355nm to 1064nm
- Broad Transmission Range
- [OD 6.0 Notch Filters Also Available](#)
- Low Cost Alternative to Rugate Notch Filters

TECHSPEC® OD 4.0 Notch Filters are low-cost alternatives to Rugate Notch Filters. The filters feature narrow rejection bands of just ±2.5% of the center wavelength while offering greater than 99% reflection of the laser wavelength. These optical filters have a broad transmission range and are hard coated to guarantee performance that will not degrade with time, temperature, or humidity. TECHSPEC® OD 4.0 Notch Filters are mounted in a black anodized ring


engraved to ease filter handling, identification, and orientation. [OD 6.0 Notch Filters](#) are also available for purchase.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information



This graph is an example of a standard notch filter transmission curve. For specific wavelength data, please refer to the curve PDF attached to each respective part.



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

Compatible Mounts