

## 632.8nm, 20mW Fiber-Coupled Frequency Stabilized Laser Diode



632.8nm Frequency Stabilized Laser Diodes (Free Space and Fiber-Coupled options shown)

Stock **#33-046** [CONTACT US](#)

⊖ 1 ⊕ ₹8,12,700

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹8,12,700 each
Qty 6+	₹7,31,700 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

**Warm-Up Time (minutes):**  
2.00

**Fiber Cable Type:**  
Single Mode w/3mm Dia Stainless Steel Shielding

**Type of Laser:**  
Diode

**Laser Class - CDRH:**  
IIIb

## Physical & Mechanical Properties

71.0 L x 63.5 W x 19.8 H  
**Dimensions (mm):**

135.00  
**Weight (g):**

1  
**Length of Fiber (m):**

<50 (8 Hours)  
**Pointing Stability (μrad):**

## Optical Properties

0.13  
**Numerical Aperture NA:**

4.3 MFD  
**Fiber Diameter (μm):**

632.80  
**Wavelength (nm):**

±0.5  
**Wavelength Tolerance (nm):**

±0.002  
**Beam Stability (nm):**

Red  
**Color:**

<100  
**Spectral Line Width (KHz):**

## Electrical

20  
**Output Power (mW):**

1.00  
**Power Stability (%):**

Max 5  
**Power Consumption (W):**

±20  
**Output Power Tolerance (%):**

10 Hz - 100 MHz 0.2% RMS  
**Noise Level:**

Max 2 @ 3.3 V  
**Input Current (A):**

## Hardware & Interface Connectivity

10-pin Connectors (cable provided upon request)  
**Electrical Leads/ Pin Connections:**

USB  
**Computer Interface:**

Fiber-Coupled  
**Output Type:**

FC/APC  
**Connector:**

## Environmental & Durability Factors

+15 to +40  
**Operating Temperature (°C):**

5 - 95% (non-condensing)  
**Operating Humidity:**

## Regulatory Compliance

[View](#)  
**Certificate of Conformance:**

United States  
**Country of Origin:**

Edmund Optics India Private Limited  
**Imported By:**

## Product Details

- Single Longitudinal Mode (SLM) Performance
- ±0.002nm Wavelength Stability
- Very Low Power Consumption

632.8nm Frequency Stabilized Laser Diodes are ideal for typical HeNe laser applications including flow cytometry, interferometry, confocal microscopy, fluorescence excitation, and Raman spectroscopy. Whereas a comparable HeNe laser would be larger, more expensive, and consume more power, the 632.8nm Frequency Stabilized Laser Diodes feature more compact designs, ±0.002nm wavelength stability, and either greater than 60mW power (free-space model) or greater than 20mW power (fiber coupled model). Additionally, these lasers utilize Variable Bragg Gratings (VBG) to lock the 632.8nm wavelength to a 10MHz linewidth.

