

[See all 67 Products in Family](#)

LightPath 354240 | 633nm Alignment, 0.50 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-727** **8 In Stock**

-

1

+

₹19,170

ADD TO CART

Volume Pricing	
Qty 1-10	₹19,170 each
Qty 11-25	₹16,920 each
Qty 26-49	₹16,020 each
Need More?	Request Quote

Product Downloads

General	
354240	Lightpath Lens Code:
Fiber Collimator	Type:

Lens Included:	
#37-103	
Physical & Mechanical Properties	
Clear Aperture CA (mm):	
8.00	
Bevel:	
Protective as needed	
Construction:	
304L Stainless Steel Housing	
Housing Diameter (mm):	
12.00	
Housing Length (mm):	
12.7	
Optical Properties	
Effective Focal Length EFL (mm):	
8.00 @ 780nm	
Numerical Aperture NA:	
0.50	
Substrate: □	
ECO-550	
Coating:	
BBAR (600-1050nm)	
Coating Specification:	
R _{abs} <1.0% @ 600 - 1050nm	
Surface Quality:	
40-20	
f#:	
1.00	
Wavelength Range (nm):	
600 - 1050	
Conjugate Distance:	
Infinite	
Alignment Wavelength (nm):	
633	
Transmitted Wavefront Error (λ, RMS):	
< 0.080	
Hardware & Interface Connectivity	
Connector:	
SMA	
Threading & Mounting	
Mount:	
M12 x 0.5	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	
Country of Origin:	
China	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

