

6.3mm Dia. x 9mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#34-455** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹2,741.00

ADD TO CART

Qty 1-10
₹2,741.00
Qty 11+
₹2,427.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.30 +/-0.3

Effective Focal Length EFL (mm):
9.00 @ 587.6nm

Numerical Aperture NA:
0.35

Back Focal Length BFL (mm): 7.90
Substrate:  Liba2000+
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 5.00
Edge Thickness ET (mm): 0.6
Center Thickness CT (mm): 1.70 ±0.20
f/#: 1.43
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 6.3
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant