

[See all 62 Products in Family](#)

# Coherent® StingRay™ Line Generator 1231500 | 640nm, 5mW, 45° Fan Angle

See More by [Coherent®](#)



Stock **#86-858** [CONTACT US](#)

- 1 + ₹61,200

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹61,200 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads



General

Coherent®  
**Manufacturer:**

Diode  
**Type of Laser:**

II  
**Laser Class - CDRH:**

|                                                                                                                                                                                                                                      |                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|
| 1231500                                                                                                                                                                                                                              | Model Number:                  |
| Physical & Mechanical Properties                                                                                                                                                                                                     |                                |
| <10                                                                                                                                                                                                                                  | Pointing Stability (μrad/°C):  |
| 97.80                                                                                                                                                                                                                                | Length (mm):                   |
| Optical Properties                                                                                                                                                                                                                   |                                |
| TEM <sub>00</sub>                                                                                                                                                                                                                    | Spatial Mode:                  |
| 640.00                                                                                                                                                                                                                               | Wavelength (nm):               |
| <1.5                                                                                                                                                                                                                                 | Mode Quality, M <sup>2</sup> : |
| ±6                                                                                                                                                                                                                                   | Wavelength Tolerance (nm):     |
| Red                                                                                                                                                                                                                                  | Color:                         |
| 45.00                                                                                                                                                                                                                                | Fan Angle (°):                 |
| Electrical                                                                                                                                                                                                                           |                                |
| 5                                                                                                                                                                                                                                    | Output Power (mW):             |
| Max Analog: 500                                                                                                                                                                                                                      | Modulation Frequency (kHz):    |
| Hardware & Interface Connectivity                                                                                                                                                                                                    |                                |
| Power Supply:<br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#86-878</a><br>Europe: <a href="#">#86-878</a><br>Japan: <a href="#">#86-878</a><br>Korea: <a href="#">#86-878</a><br>China: <a href="#">#86-878</a> |                                |
| Electrical Leads/ Pin Connections:<br>Hirose HR-10P-12S                                                                                                                                                                              |                                |
| Free Space                                                                                                                                                                                                                           | Output Type:                   |
| 5 - 24 DC                                                                                                                                                                                                                            | Input Voltage (V):             |
| Environmental & Durability Factors                                                                                                                                                                                                   |                                |
| -10 to +50                                                                                                                                                                                                                           | Operating Temperature (°C):    |
| -20 to +60                                                                                                                                                                                                                           | Storage Temperature (°C):      |
| Regulatory Compliance                                                                                                                                                                                                                |                                |
| <a href="#">Exempt</a>                                                                                                                                                                                                               | RoHS 2015:                     |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                                                     | Reach 224:                     |
| <a href="#">View</a>                                                                                                                                                                                                                 | Certificate of Conformance:    |
| Singapore                                                                                                                                                                                                                            | Country of Origin:             |
| Edmund Optics India Private Limited                                                                                                                                                                                                  | Imported By:                   |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

**Note:** For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5-5V) with BNC connector is required.

---

;