

[See all 18 Products in Family](#)

670nm, $\lambda/2$ Precision Zero Order Retarder



Stock #49-212 **3 In Stock**

1 MRP ₹76,173

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹76,173 each
Qty 6+	₹60,534 each
Need More?	Request Quote

Product Downloads

General

Polymer Waveplate **Type:**

Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

Diameter (mm):

25.40

±0.508 Thickness Tolerance (mm):

±0.127 Dimensional Tolerance (mm):

Birefringent Polymer Stack Construction:

Optical Properties

670 Design Wavelength DWL (nm):

Polymer Film on [N-BK7](#) Substrate:

0.5 Reflection (%):

$\lambda/2$ Retardance:

40-20 Surface Quality:

$\leq \lambda/5$ @ 632.8nm Transmitted Wavefront, RMS:

$\lambda/350$ Retardance Tolerance:

1.00 Beam Deviation (arcmin):

500 W/cm² Damage Threshold, By Design:

0 Retardance Order:

Threading & Mounting

6.35 Mount Thickness (mm):

Environmental & Durability Factors

-20 to +50 Operating Temperature (°C):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) REACH 241:

United States Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- $\lambda/4$ and $\lambda/2$ Retardance
- Excellent Angular Field of View
- Birefringent Polymer Stack
- High Damage Threshold of 500 W/cm²

Precision Zero Order Waveplates (Retarders) feature carefully aligned birefringent polymer sheets laminated between two precision N-BK7 windows, and are available in standard $\lambda/4$ and $\lambda/2$ options for common visible and NIR wavelengths. These polymer waveplates (retarders) offer excellent angular field of view because they are true zero-order retarders. Also, they will experience less than 1% retardance change over a $\pm 10^\circ$ angle of incidence. Each Precision Zero Order Waveplates (Retarders) is mounted in a metal ring with the fast axis clearly marked.