

650nm CWL, 80nm FWHM, 11.8mm Unmounted Diameter



Bandpass Interference Filters

Stock **#46-153** CLEARANCE **20+ In Stock**

-

1

+

₹3,445

ADD TO CART

Volume Pricing	
Qty 1+	₹3,445 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
>9.2	Clear Aperture CA (mm):
11.8000000000 ±0.15	Diameter (mm):
4.6000000000 ±0.5	Thickness (mm):

Optical Properties	
Traditional Coated	Coating:
650.0000000000	Center Wavelength CWL (nm):
±15	Center Wavelength CWL Tolerance (nm):
80.0000000000	Full Width-Half Max FWHM (nm):
±25	Full Width-Half Max FWHM Tolerance (nm):
60.00	Minimum Transmission (%):
≥3.0	Optical Density OD (Average):
80-50	Surface Quality:
200 - 1200	Blocking Wavelength Range (nm):
Intended for Collimated Input	Angle Sensitivity:

Environmental & Durability Factors	
-50 to +75	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

Interference filters will function with either side facing the source. We recommend, however, orienting the "mirror-like" side toward the source to minimize any thermal effects. If the source overfills the actual filter area, beam vignetting may be necessary.

- Many CWL Options Available
- Ideal for Biomedical Applications and Instrumentation Integration
- Unmounted and Mounted Versions Offered

Bandpass Interference Filters are used extensively in a variety of biotech, biomedical, and quantitative chemical applications to selectively transmit a narrow range of wavelengths while blocking all others. Interference filters are widely used in instrumentation for clinical chemistry, environmental testing, colorimetry, elemental and laser line separation, flame photometry, fluorescence, immunoassays, etc. In addition, interference filters are used to select discrete spectral lines from arc or gas discharge lamps (Hg, Xe, Cd, etc.) and to isolate a particular line from Ar, Kr, Nd:YAG, and other lasers. Bandpass Interference Filters are often used in conjunction with laser diodes and LEDs. The filters are available with traditional coating and in 11.80 or 12.70mm diameters.

Note: Interference filters will function with either side facing the source. We recommend, however, orienting the "mirror-like" side toward the source to minimize any thermal effects. Beam vignetting may be necessary if the source overfills the actual filter area.