

676nm CWL, 11.8mm Dia. Bandpass Filter



Stock #28-484 CLEARANCE 20+ In Stock

-

1

+

₹1,736

ADD TO CART

Volume Pricing	
Qty 1+	₹1,736 each
Need More?	Request Quote

Product Downloads

General

Type:	
Bandpass Filter	
Typical Applications:	
Kr Emission Line	

Physical & Mechanical Properties

Diameter (mm):	
11.80	
Thickness (mm):	
4.60	

Dimensional Tolerance (mm):

±0.2	
Optical Properties	
≥3.0	Optical Density OD (Average):
676.00	Center Wavelength CWL (nm):
±2	Center Wavelength CWL Tolerance (nm):
10.00	Full Width-Half Max FWHM (nm):
50	Minimum Transmission (%):
80-50	Surface Quality:
200 - 1200	Blocking Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ideal for Selectively Transmitting a Narrow Range of Wavelengths
- Quantities Extremely Limited, Buy While Supplies Last
- For Even Mbre Deals, Check out [Mega Clearance: Optics](#)

Bandpass interference filters are used extensively in a variety of biotech, biomedical, or quantitative chemical applications to selectively transmit a narrow range of wavelengths while blocking all others. Experimental Grade Bandpass Interference Filters are available in a variety of bandpass ranges in 11.8mm and 24.15mm diameter unmounted options.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

