

## 6.7" x 6.7", FL 2.8", IR Fresnel Lens



Infrared (IR) Fresnel Lenses

Stock **#43-798** **1 In Stock**

1  MRP ₹4,792

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-10	₹4,792 each
Qty 11-49	₹4,339 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Fresnel Lens **Type:**

### Physical & Mechanical Properties

0.02 **Center Thickness CT (inches):**

6.7 x 6.7 **Dimensions (inches):**

170.18 x 170.18	<b>Dimensions (mm):</b>
6.0	<b>Effective Diameter (inches):</b>
0.40 - 1.24	<b>Young's Modulus (GPa):</b>

## Optical Properties

71.12	<b>Effective Focal Length EFL (mm):</b>
Poly IR	<b>Substrate:</b> <input type="checkbox"/>
Uncoated	<b>Coating:</b>
8000 - 14000	<b>Wavelength Range (nm):</b>
2.80	<b>Effective Focal Length EFL (inches):</b>
100.00	<b>Groove Density (grooves/inch):</b>
Visible (Sodium D Line): 1.52 8-14µm: 1.53 15µm+: 1.48	<b>Index of Refraction (n<sub>d</sub>):</b>
8 - 14	<b>Wavelength Range (µm):</b>

## Material Properties

11 - 13	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
(100-260) x 10 <sup>3</sup>	<b>Flexural Modulus (psi):</b>
D60-70	<b>Shore Hardness:</b>

## Environmental & Durability Factors

100.00	<b>Operating Temperature (°C):</b>
--------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>


## Product Details

- Excellent Collecting Optics for Infrared Detectors
- Minimal Absorption Loss in the 8-14µm Region


IR Fresnel lenses are molded in a flexible, 0.015" (0.457mm) thick, milky white plastic. Advantages of this product are: least absorption loss in the 8-14µm region, extremely thin with consistent thickness across the lens, large apertures and minimal thermal expansion. The design of an infrared-transmitting Fresnel lens involves many complex considerations. The grooved side of a Fresnel lens should face the longer conjugate (away from the detector when used to collect radiation). If the smooth side needs to face the longer conjugate for some nonoptical reason, the maximum aperture of the lens should be f/1.0. In this case, total internal reflection keeps all radiation from the area of the lens past f/1.0 from reaching the image. Even when the grooves face the longer conjugate, the portion of the lens past f/1.0 contributes a diminished amount and there is no significant contribution past f/0.5.

## Technical Information

**IR Windows in the IR Spectrum**



**IR Windows in the Visible Spectrum**



Effect of Sunlight	None to Slight
Effect of Ultraviolet	UV Stabilized
Effect of Weak Acids	Very Little
Effect of Strong Acids	Attacked by Oxidizing Acids
Effect of Weak Alkalies	Very Little
Effect of Strong Alkalies	Very Little
Effect of Organic Solvents	Little below 60°C (140°F)