

[See all 102 Products in Family](#)

6.5mm Diameter x 6mm FL, MgF₂ Coated, PCX Condenser Lens



Stock #15-527 **2 In Stock**

[Other Coating Options](#)

1 MRP ₹4,187

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹4,187 each |
| Qty 11-49 | ₹3,834 each |
| Need More? | Request Quote |

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

6.50 **Diameter (mm):**

3.75 ±0.1 **Center Thickness CT (mm):**

Protective as needed **Bevel:**
Plano **Shape of Back Surface:**

Optical Properties

6.00 **Effective Focal Length EFL (mm):**

0.58 **Numerical Aperture NA:**

Float Glass **Substrate:** □

±7 **Focal Length Tolerance (%):**

MgF₂ (400-700nm) **Coating:**

R_{avg} ≤ 1.75% @ 400 - 700nm **Coating Specification:**

80-50 (typical) **Surface Quality:**

0.86 **f#:**

Plano **Radius R₂ (mm):**

400 - 700 **Wavelength Range (nm):**

Infinite **Conjugate Distance:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

United States **Country of Origin:**


Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information





Coating Curves
