

**TECHSPEC® 6mm Dia. x 18mm FL, UV-AR Coated, UV Double-Convex Lens**



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-987** 10 TO 12 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

**₹11,310.00**

ADD TO CART

Qty 1-5

₹11,310.00

Qty 6+

₹9,048.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Diameter (mm):**  
6.00 +0.0/-0.025

**Back Focal Length BFL (mm):**

|                                                                                                                                                        |
|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 17.30                                                                                                                                                  |
| <b>Effective Focal Length EFL (mm):</b><br>18.00                                                                                                       |
| <b>Coating:</b><br>UV-AR (250-425nm)                                                                                                                   |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.0% @ 250 - 425nm<br>R <sub>avg</sub> ≤0.75% @ 250 - 425nm<br>R <sub>avg</sub> ≤0.5% @ 370 - 420nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)                                                              |
| <b>Surface Quality:</b><br>40-20                                                                                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                            |
| <b>Centering (arcmin):</b><br><1                                                                                                                       |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                            |
| <b>Center Thickness CT (mm):</b><br>2.00 ±0.05                                                                                                         |
| <b>Edge Thickness ET (mm):</b><br>1.44                                                                                                                 |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>16.18                                                                                               |
| <b>Clear Aperture CA (mm):</b><br>5.4                                                                                                                  |
| <b>f/#:</b><br>3.00                                                                                                                                    |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                                                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                               |
| <b>Numerical Aperture NA:</b><br>0.17                                                                                                                  |
| <b>Type:</b><br>Double-Convex Lens                                                                                                                     |
| <b>Wavelength Range (nm):</b><br>250 - 425                                                                                                             |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>3 J/cm <sup>2</sup> @ 355nm, 10ns                                                      |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |