

[See all 245 Products in Family](#)

TECHSPEC<sup>®</sup> 6mm Dia. x 24mm FL, VIS 0° Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-996** **13 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹10,198

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹10,198 each                  |
| Qty 6-25       | ₹8,174 each                   |
| Qty 26-49      | ₹7,629 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| 6.00 +0.0/-0.025     |                           |
| <1                   | Centering (arcmin):       |
|                      | Bevel:                    |
| Protective as needed |                           |
|                      | Center Thickness CT (mm): |
| 2.00 ±0.05           |                           |
|                      | Edge Thickness ET (mm):   |
| 1.58                 |                           |
|                      | Clear Aperture CA (mm):   |
| 5.4                  |                           |

|                                      |                                                       |
|--------------------------------------|-------------------------------------------------------|
| Optical Properties                   |                                                       |
|                                      | Back Focal Length BFL (mm):                           |
| 23.31                                |                                                       |
|                                      | Effective Focal Length EFL (mm):                      |
| 24.00                                |                                                       |
|                                      | Coating:                                              |
| VIS 0° (425-675nm)                   |                                                       |
|                                      | Coating Specification:                                |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm |                                                       |
|                                      | Substrate: <input type="checkbox"/>                   |
| Fused Silica (Corning 7980)          |                                                       |
|                                      | Surface Quality:                                      |
| 40-20                                |                                                       |
|                                      | Power (P-V) @ 632.8nm:                                |
| 1.5λ                                 |                                                       |
|                                      | Irregularity (P-V) @ 632.8nm:                         |
| λ/4                                  |                                                       |
|                                      | Radius R <sub>1</sub> =R <sub>2</sub> (mm):           |
| 21.69                                |                                                       |
|                                      | f/#:                                                  |
| 4.00                                 |                                                       |
|                                      | Focal Length Specification Wavelength (nm):           |
| 587.6                                |                                                       |
|                                      | Focal Length Tolerance (%):                           |
| ±1                                   |                                                       |
|                                      | Numerical Aperture NA:                                |
| 0.13                                 |                                                       |
|                                      | Wavelength Range (nm):                                |
| 425 - 675                            |                                                       |
|                                      | Damage Threshold, Reference: <input type="checkbox"/> |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns    |                                                       |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
|                                     | RoHS 2015:                  |
| Compliant                           |                             |
|                                     | Certificate of Conformance: |
| View                                |                             |
|                                     | Reach 235:                  |
| Compliant                           |                             |
|                                     | Country of Origin:          |
| Japan                               |                             |
|                                     | Imported By:                |
| Edmund Optics India Private Limited |                             |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate




TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging



applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.

Technical Information







UV FS Transmission Curve



| FUSED SILICA                                                                                                                                                                  |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Uncoated Fused Silica<br/>Typical Transmission</div> <div></div>                     |  | <div>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                                                                                                                                                                                                   |
| <div>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</div> <div></div> |  | <div>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><math>R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}</math></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |

|                                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| <div>2004006008001000120014001600180020002200</div> <div>Wavelength (nm)</div>                                                                                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |
| <div>Fused Silica with UV-AR Coating</div> <div>Typical Transmission</div> <div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div></div><div>Wavelength (nm)</div></div></div>                                 | <p>Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div><div><div><math>R_{abs} \leq 1.0\%</math> @ 250 - 425nm</div><div><math>R_{avg} \leq 0.75\%</math> @ 250 - 425nm</div><div><math>R_{avg} \leq 0.5\%</math> @ 370 - 420nm</div></div></div> <p>Data outside this range is not guaranteed and is for reference only.</p> <div><a href="#">Click Here to Download Data</a></div> |  |
| <div>Fused Silica with UV-VIS Coating</div> <div>Typical Transmission</div> <div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div></div><div>Wavelength (nm)</div></div></div>                                | <p>Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div><div><div><math>R_{abs} \leq 1.0\%</math> @ 350 - 450nm</div><div><math>R_{avg} \leq 1.5\%</math> @ 250 - 700nm</div></div></div> <p>Data outside this range is not guaranteed and is for reference only.</p> <div><a href="#">Click Here to Download Data</a></div>                                                         |  |
| <div>Fused Silica with VIS-EXT Coating</div> <div>Typical Transmission</div> <div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div></div><div>Wavelength (nm)</div></div></div>                               | <p>Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div><div><div><math>R_{avg} \leq 0.5\%</math> @ 350 - 700nm</div></div></div> <p>Data outside this range is not guaranteed and is for reference only.</p> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                |  |
| <div>Fused Silica with VIS-NIR Coating</div> <div>Typical Transmission</div> <div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div></div><div>Wavelength (nm)</div></div></div> | <p>Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div><div><div><math>R_{abs} \leq 0.25\%</math> @ 880nm</div><div><math>R_{avg} \leq 1.25\%</math> @ 400 - 870nm</div><div><math>R_{avg} \leq 1.25\%</math> @ 890 - 1000nm</div></div></div> <p>Data outside this range is not guaranteed and is for reference only.</p> <div><a href="#">Click Here to Download Data</a></div> |  |

|                                                                                                                                                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div data-bbox="231 74 1306 765"><h3>Fused Silica with VIS 0° Coating<br/>Typical Transmission</h3></div>       | <div data-bbox="1306 74 1869 765"><p>Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.4\% @ 425 - 675nm</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                             |
| <div data-bbox="231 765 1306 1430"><h3>Fused Silica with YAG-BBAR Coating<br/>Typical Transmission</h3></div> | <div data-bbox="1306 765 1869 1430"><p>Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 0.25\% @ 532nm</math><br/><math>R_{abs} \leq 0.25\% @ 1064nm</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100nm</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>            |
| <div data-bbox="231 1430 1306 2116"><h3>Fused Silica with NIR I Coating<br/>Typical Transmission</h3></div>  | <div data-bbox="1306 1430 1869 2116"><p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.5\% @ 600 - 1050nm</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                       |
| <div data-bbox="231 2116 1306 2783"><h3>Fused Silica with NIR II Coating<br/>Typical Transmission</h3></div> | <div data-bbox="1306 2116 1869 2783"><p>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 1.5\% @ 750 - 800nm</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550nm</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550nm</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |

Coating Curves

Compatible Mounts

;