

TECHSPEC[®] 6mm Dia. x 30mm FL Uncoated, Double-Convex Lens



Stock **#45-133** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹2,480.00

ADD TO CART

Qty 1-9
₹2,480.00
Qty 10+
₹2,240.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Back Focal Length BFL (mm):
29.23

Effective Focal Length EFL (mm): 30.00
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.30
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.00
Radius R₁=R₂ (mm): 30.61
Clear Aperture CA (mm): 5.4
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant