

TECHSPEC®

6mm Dia. x 24mm FL, VIS 0° Inked, Double-Convex Lens



Stock **#47-482-INK** 17 TO 22 D= DAYS

[Other Coating Options](#)



1



₹4,307.00

ADD TO CART

Qty 1-9
₹4,307.00
Qty 10+
₹3,872.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Back Focal Length BFL (mm):
23.13

Effective Focal Length EFL (mm): 24.00
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.23
Radius R₁=R₂ (mm): 24.36
Clear Aperture CA (mm): 5.4
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View