

TECHSPEC[®] 6mm Dia. x 25mm FL, NIR II Coated, Achromatic Lens



Stock #45-787 10 TO 12 DAYS

-

1

+

₹8,874.00

ADD TO CART

Qty 1-5
₹8,874.00
Qty 6+
₹7,091.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 22.24
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 5.4
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.30 ±0.10
Center Thickness CT 1 (mm) : 3.00 ±0.05
Center Thickness CT 2 (mm) : 1.30 ±0.05
Radius R₁ (mm) : 13.95
Radius R₂ (mm) : -13.40
Radius R₃ (mm) : -193.19
Edge Thickness ET (mm) : 3.95
Substrate: ☐ N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 4.17
Numerical Aperture NA : 0.12
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 750 - 1550

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View