

TECHSPEC® 6mm Dia. x 9mm FL, UV-AR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-247** [CONTACT US](#)

[Other Coating Options](#)

- 1 +

₹11,745.00

ADD TO CART

Qty 1-5

₹11,745.00

Qty 6+

₹9,396.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Back Focal Length BFL (mm):

8.02
Effective Focal Length EFL (mm): 9.00
Coating: UV-AR (250-425nm)
Coating Specification: R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.70 ±0.05
Edge Thickness ET (mm): 1.50
Radius R₁=R₂ (mm): 7.80
Clear Aperture CA (mm): 5.4
f/#: 1.5
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.33
Type: Double-Convex Lens
Wavelength Range (nm): 250 - 425
Damage Threshold, Reference: ☐ 3 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant