

TECHSPEC[®] 6mm Dia. x -6mm FL, NIR II Coated, Double-Concave Lens



Stock #68-005 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹3,350.00

ADD TO CART

Qty 1-9
₹3,350.00
Qty 10+
₹3,023.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-6.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: NIR II (750-1550nm)
Type: Double-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -6.41
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.40
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 2.29
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁=R₂ (mm): -9.74
Surface Quality: 40-20
Damage Threshold, By Design: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View