

[See all 245 Products in Family](#)

TECHSPEC[®] 6mm Dia. x 6mm FL, Uncoated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#49-238** 20+ In Stock

[Other Coating Options](#)

-

1

+

₹9,108

ADD TO CART

Volume Pricing	
Qty 1-5	₹9,108 each
Qty 6-25	₹7,318 each
Qty 26-49	₹6,851 each
Need More?	Request Quote

Product Downloads

General

Double-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

6.00 +0.0/-0.025	
Centering (arcmin):	<1
Bevel:	Protective as needed
Center Thickness CT (mm):	4.10 ±0.05
Edge Thickness ET (mm):	1.97
Clear Aperture CA (mm):	5.4

Optical Properties	
Back Focal Length BFL (mm):	4.38
Effective Focal Length EFL (mm):	6.00
Coating:	Uncoated
Coating Specification:	Uncoated
Substrate: ☐	Fused Silica (Corning 7980)
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4
Radius R ₁ =R ₂ (mm):	4.76
f#:	1.00
Focal Length Specification Wavelength (nm):	587.6
Focal Length Tolerance (%):	±1
Numerical Aperture NA:	0.50
Wavelength Range (nm):	200 - 2200

Regulatory Compliance	
RoHS 2015:	Compliant
Reach 219:	Compliant
Certificate of Conformance:	View
Country of Origin:	Italy
Imported By:	Edmund Optics India Private Limited

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Imaging Applications
- Minimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate





TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.

Technical Information



UV FS Transmission Curve

FUSED SILICA																											
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmittance (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90	Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data		
Wavelength (nm)	Transmittance (%)																										
200	92																										
400	94																										
600	94																										
800	94																										
1000	94																										
1200	94																										
1400	92																										
1600	94																										
1800	94																										
2000	94																										
2200	90																										
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for MgF2 Coated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>96</td></tr><tr><td>600</td><td>96</td></tr><tr><td>800</td><td>96</td></tr><tr><td>1000</td><td>96</td></tr><tr><td>1200</td><td>96</td></tr><tr><td>1400</td><td>94</td></tr><tr><td>1600</td><td>96</td></tr><tr><td>1800</td><td>96</td></tr><tr><td>2000</td><td>96</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table>	Wavelength (nm)	Transmittance (%)	200	94	400	96	600	96	800	96	1000	96	1200	96	1400	94	1600	96	1800	96	2000	96	2200	90	Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm (N-BK7)}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data		
Wavelength (nm)	Transmittance (%)																										
200	94																										
400	96																										
600	96																										
800	96																										
1000	96																										
1200	96																										
1400	94																										
1600	96																										
1800	96																										
2000	96																										
2200	90																										
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for UV-AR Coated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>80</td></tr><tr><td>250</td><td>99</td></tr><tr><td>400</td><td>99</td></tr><tr><td>600</td><td>99</td></tr><tr><td>800</td><td>99</td></tr><tr><td>1000</td><td>99</td></tr><tr><td>1200</td><td>99</td></tr><tr><td>1400</td><td>99</td></tr><tr><td>1600</td><td>99</td></tr><tr><td>1800</td><td>99</td></tr><tr><td>2000</td><td>99</td></tr><tr><td>2200</td><td>80</td></tr></tbody></table>	Wavelength (nm)	Transmittance (%)	200	80	250	99	400	99	600	99	800	99	1000	99	1200	99	1400	99	1600	99	1800	99	2000	99	2200	80	Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only.
Wavelength (nm)	Transmittance (%)																										
200	80																										
250	99																										
400	99																										
600	99																										
800	99																										
1000	99																										
1200	99																										
1400	99																										
1600	99																										
1800	99																										
2000	99																										
2200	80																										

	Click Here to Download Data
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

20040060080010001200 Wavelength (nm)	
Fused Silica with YAG-BBAR Coating Typical Transmission T (%) 100959085807570 2004006008001000120014001600 Wavelength (nm)	Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR I Coating Typical Transmission T (%) 100959085807570 2004006008001000120014001600 Wavelength (nm)	Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with NIR II Coating Typical Transmission T (%) 100959085807570 200400600800100012001400160018002000 Wavelength (nm)	Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

Compatible Mounts