

[See all 26 Products in Family](#)

TECHSPEC® 6mm Dia. x -6mm FL, VIS-NIR, Inked, Double-Concave Lens



Stock **#45-927-INK** [CONTACT US](#)

- 1 + MRP ₹6,053

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | ₹6,053 each |
| Qty 10-25 | ₹5,469 each |
| Qty 26-49 | ₹4,832 each |
| Need More? | Request Quote |

Product Downloads

General

Double-Concave Lens **Type:**

Physical & Mechanical Properties

6.00 **Diameter (mm):**

| | |
|--|---|
| Protective as needed | Bevel: |
| 1.50 | Center Thickness CT (mm): |
| ±0.05 | Center Thickness Tolerance (mm): |
| <3 | Centering (arcmin): |
| 5.4 | Clear Aperture CA (mm): |
| 2.26 | Edge Thickness ET (mm): |
| Optical Properties | |
| -6.00 | Effective Focal Length EFL (mm): |
| N-SF11 | Substrate: <input type="checkbox"/> |
| 1.00 | f#: |
| 0.50 | Numerical Aperture NA: |
| VIS-NIR (400-1000nm) | Coating: |
| 400 - 1000 | Wavelength Range (nm): |
| -6.41 | Back Focal Length BFL (mm): |
| R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm | Coating Specification: |
| ±1 | Focal Length Tolerance (%): |
| -9.74 | Radius R₁=R₂ (mm): |
| 40-20 | Surface Quality: |

Regulatory Compliance

| | |
|---|------------------------------------|
| View | Certificate of Conformance: |
| Japan | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- <0.25% Reflectance @ 880nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), and [NIR II](#)

TECHSPEC® VIS-NIR Coated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® VIS-NIR Coated Double-Concave (DCV) Lenses are optimized for transmission (>99%) in the near-infrared. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), or with [NIR II](#) AR coating options.

Technical Information



Coating Curves

Compatible Mounts