

**TECHSPEC® 6mm, f/2.8 Cw Series Fixed Focal Length Lens**



6mm Focal Length



Stock #15-621 **20+ In Stock**

MRP ₹31,405

**Price inclusive of all taxes**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹31,405 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Cw Series **Product Family:**

C-Mount compatible with O-ring 25mm ID x2mm **Note:**

Fixed Focal Length Lens **Type:**

## Physical & Mechanical Properties

|       |                               |
|-------|-------------------------------|
| Fixed | Iris Option:                  |
| 51.40 | Length (mm):                  |
| 46.00 | Maximum Diameter (mm):        |
| 46    | Outer Diameter (mm):          |
| 1.2   | Maximum Rear Protrusion (mm): |

## Optical Properties

|                                     |  |
|-------------------------------------|--|
| Field of View at Max Sensor Format: |  |
| Horizontal: 62.1°                   |  |
| Vertical: 47.7°                     |  |
| Diagonal: 75.0°                     |  |
| 62.1°                               | Horizontal Field of View, 1/1.8" Sensor: |
| 55.8°                               | Horizontal Field of View, 1/2" Sensor:   |
| 50.7°                               | Horizontal Field of View, 1/2.5" Sensor: |
| 42.7°                               | Horizontal Field of View, 1/3" Sensor:   |
| 9.00                                | Maximum Image Circle (mm):               |
| 0.0110                              | Numerical Aperture NA, Object Side:      |
| 10 (9)                              | Number of Elements (Groups):             |
| 6.00                                | Focal Length FL (mm):                    |
| 75 - ∞                              | Working Distance (mm):                   |
| f/2.8                               | Aperture (f/#):                          |
| 425 - 675nm BBAR                    | Coating Specification:                   |
| 21.52                               | Entrance Pupil Position (mm):            |
| -33.64                              | Object Space Principal Plane (mm):       |
| 22.43                               | Image Space Principal Plane (mm):        |
| 6.869                               | Maximum Distortion (%):                  |
| -25.51                              | Exit Pupil Position (mm):                |
| VS                                  | Lens Wavelength Range:                   |

## Sensor

|        |                        |
|--------|------------------------|
| 1/1.8" | Maximum Sensor Format: |
| 2.74   | Pixel Size (μm):       |

## Threading & Mounting

|                       |                |
|-----------------------|----------------|
| M30.5 x 0.50 (Female) | Filter Thread: |
| C-Mount               | Mount:         |

## Environmental & Durability Factors

|                             |                           |
|-----------------------------|---------------------------|
| IPX7 and IPX9K              | Environmental Rating:     |
| -20 to +60                  | Storage Temperature (°C): |
| Waterproof (IPX7 and IPX9K) | Type of Ruggedization:    |

## Regulatory Compliance

**Country of Origin:**

China

**Imported By:**

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

## Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


## Technical Information




#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Distortion Plot




#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f2.8



#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f2.8



#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2.8



#15-621, 6mm, f/2.8 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2.8