

TECHSPEC[®] 6mm Dia. x -9mm FL, VIS 0° Coated, Double-Concave Lens



Stock **#48-938** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹3,114

ADD TO CART

Volume Pricing	
Qty 1-9	₹3,114 each
Qty 10-25	₹2,803 each
Qty 26-49	₹2,491 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Double-Concave Lens	
Physical & Mechanical Properties	
6.00 +0.0/-0.025	Diameter (mm):
Protective as needed	Bevel:
Center Thickness CT (mm):	
1.00	
Center Thickness Tolerance (mm):	
±0.05	
Centering (arcmin):	
<3	
Clear Aperture CA (mm):	
5.4	
Edge Thickness ET (mm):	
1.79	
Optical Properties	
Effective Focal Length EFL (mm):	
-9.00	
N-BK7	Substrate: ☐
f#:	
1.5	
Numerical Aperture NA:	
0.33	
Coating:	
VIS 0° (425-675nm)	
Wavelength Range (nm):	
425 - 675	
Back Focal Length BFL (mm):	
-9.32	
Coating Specification:	
R _{avg} ≤0.4% @ 425 - 675nm	
Focal Length Specification Wavelength (nm):	
587.6	
Focal Length Tolerance (%):	
±1	
Radius R ₁ =R ₂ (mm):	
-9.47	
Surface Quality:	
40-20	
Damage Threshold, Reference: ☐	
5 J/cm ² @ 532nm, 10ns	
Power (P-V) @ 632.8nm:	
1.5λ	
Irregularity (P-V) @ 632.8nm:	
λ/4	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	

PRODUCT DETAILS

- AR Coated to Provide <0.4% Reflectance per Surface for 425 - 675nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® VIS 0° Coated Double-Concave (DCV) Lenses are best used in 0° angle of incidence situations and provide optimized transmission in the 425nm – 675nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF₂](#), [VIS-NIR](#), [NIR I](#), or with [NIR II](#) AR coating options.

TECHNICAL INFORMATION



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS