

6mm Diameter, Extended B270 Half-Ball Lens



B270 Half-Ball Lenses

Stock **#21-907** **3 In Stock**

-

1

+

₹2,627

ADD TO CART

Volume Pricing	
Qty 1-10	₹2,627 each
Qty 11-25	₹2,102 each
Qty 26-49	₹1,888 each
Need More?	Request Quote

Product Downloads

General	
Half-Ball Lens	Type:
Physical & Mechanical Properties	
6.00 ±0.1	Diameter (mm):
3.30 ±0.15	Center Thickness CT (mm):

3.00	Radius R (mm):
Optical Properties	
B270	Substrate: ☐
Uncoated	Coating:
360 - 2700	Wavelength Range (nm):
1.523	Index of Refraction (n _d):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

B270 Half-Ball Lenses feature a molded spherical surface and polished plano surface, facilitating easier mounting compared to ball lenses. The B270 substrates have high transmission from the visible to the near infrared (NIR) and have a similar refractive index to N-BK7, making these lenses an ideal alternative for cost sensitive applications. Each diameter of lens is available in two form factors, truncated (hypo-hemisphere) and extended (hyper-hemisphere), providing options to best meet system mechanical requirements. B270 Half-Ball Lenses are used in high power LED, fiber coupling, endoscopy, microscopy, and laser measurement applications.