

[See all 49 Products in Family](#)

TECHSPEC® 6mm, f/8 UCi Series Fixed Focal Length Lens



6mm UCi Series Fixed Focal Length Lens



Stock **#33-866** **1 In Stock**

MRP ₹23,440

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹23,440 each
Need More?	Request Quote

Product Downloads

General

UCi Series **Product Family:**

Fixed Focal Length Lens **Type:**

No **IR Cut Filter:**

Physical & Mechanical Properties

Fixed Iris Option:

47.30 Length (mm):

30.5 Maximum Diameter (mm):

30.5 Outer Diameter (mm):

52 Weight (g):

0 Maximum Rear Protrusion (mm):

Optical Properties

72.8mm - 60.0° Horizontal Field of View @ Max Sensor Format:

Field of View at Max Sensor Format:
Horizontal: 72.8mm - 60°
Vertical: 52.7mm - 45.4°
Diagonal: 95.5mm - 73.8°

72.8mm - 60.0° Horizontal Field of View, 1/2" Sensor:

65.0mm - 54.6° Horizontal Field of View, 1/2.5" Sensor:

52.7mm - 45.4° Horizontal Field of View, 1/3" Sensor:

38.7mm - 34.2° Horizontal Field of View, 1/4" Sensor:

8.00 Maximum Image Circle (mm):

0.0059 Numerical Aperture NA, Object Side:

9 (8) Number of Elements (Groups):

6.00 Focal Length FL (mm):

50 - ∞ Working Distance (mm):

f/8.0 Aperture (f#):

M4 MgF₂ Coating:

M4 MgF₂ Coating Specification:

12.61 Entrance Pupil Position (mm):

17.55 Object Space Principal Plane (mm):

4.85 Image Space Principal Plane (mm):

-11.2 Maximum Distortion (%):

-23.26 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

Sensor

1/2.5" Optimized Sensor Format:

1/2" Maximum Sensor Format:

1.85 Pixel Size (μm):

Threading & Mounting

M30.5 x 0.50 (Male) Filter Thread:

S-Mount (M12 x 0.5) Mount:

Environmental & Durability Factors

Storage Temperature (°C):

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Up to 1/1.8", C-Mount, S-Mount Lens
- Up to 12 MegaPixels, 1.85µm Pixel Size Sensors
- Instrumentation (UCi) versions of our UC Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 4mm to 35mm Focal Length

TECHSPEC® UCi Series Fixed Focal Length Lenses utilize the same optics as the TECHSPEC UC Series Lenses and feature 4K resolution. These lenses are designed for small pixels $\leq 2.2\mu\text{m}$ and offer a wide range of fixed apertures for a variety of applications. While optimized for 1/2.5" sensors, many focal length options can be used on sensors up to 1/1.8". TECHSPEC® UCi Series Fixed Focal Length Lenses are ideal for OEM applications that require small, robust, and lightweight imaging solutions.

Note: For adjustable aperture options, see our [TECHSPEC® UC Series Fixed Focal Length Lenses](#).

Edmund Optics has created a family of high-performance ultra-compact optical designs (the UC Series family) and developed 3 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the UC Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:


UC Series: Features locking cam focus and iris adjustment in an ultra-compact design and is the most adjustable version of these optical designs; they are the typical high-quality machine vision lenses.

UCi Series: Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.


UCr Series: All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

UCw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 to withstand exposure to water up to 1 meter depth for 30 minutes.


Technical Information




#33-866, 6mm, f/8 UCi Series Fixed Focal Length Lens, Distortion Plot




#33-866, 6mm, f/8 UCi Series Fixed Focal Length Lens, Relative Illumination Plot




#33-866, 6mm, f/8 UCi Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#33-866, 6mm, f/8 UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f8



#33-866, 6mm, f/8 UCI Series Fixed Focal Length Lens, Depth of Field Plot, 150mm Working Distance, f8



#33-866, 6mm, f/8 UCI Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 850mm Working Distance, f8



#33-866, 6mm, f/8 UCI Series Fixed Focal Length Lens, Depth of Field Plot, 850mm Working Distance, f8

Compatible Cameras