See all 76 Products in Family

TECHSPEC® 6mm, f/4 Ci Series Fixed Focal Length Lens

6mm Focal Length

Stock **#86-594** **3 In Stock**

- 1 +

MRP ₹20,481

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	**₹20,481** each
Qty 25+	**₹18,442** each
Need More?	Request Quote

Product Downloads

General

Product Family:
Ci Series

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Fixed

Length (mm):
47.80

Maximum Diameter (mm):
34

Outer Diameter (mm):
34

Weight (g):
64

Maximum Rear Protrusion (mm):
1.17

Diameter (mm):
26.50

Optical Properties

Horizontal Field of View @ Max Sensor Format:
110.2mm - 62.1°

Field of View at Max Sensor Format:
Horizontal: 110mm - 62.1°
Vertical: 80.4mm - 47.8°
Diagonal: 141.9mm - 75°

Horizontal Field of View, 1/1.8" Sensor:
110.2mm - 62.1°

Horizontal Field of View, 1/2" Sensor:
96.8mm - 55.9°

Horizontal Field of View, 1/2.5" Sensor:
86.9mm - 51.0°

Horizontal Field of View, 1/3" Sensor:
71.0mm - 42.7°

Horizontal Field of View, 1/4" Sensor:
52.6mm - 32.4°

Maximum Image Circle (mm):
9.00

Numerical Aperture NA, Object Side:
0.0086

Number of Elements (Groups):
9 (7)

Focal Length FL (mm):
6.00

Working Distance (mm):
75 - ∞

Aperture (f/#):
f/4

Coating:
425 - 675nm BBAR

Coating Specification:
425 - 675nm BBAR

Entrance Pupil Position (mm):
16.08

Object Space Principal Plane (mm):
21.35

Image Space Principal Plane (mm):
6.60

Maximum Distortion (%):
-6.82

Exit Pupil Position (mm):
-25.52

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/1.8"

Pixel Size (µm):
2.74

Threading & Mounting

Filter Thread:
M43 x 0.75 (Female)

Filter Thread Adapter:
#89-940 (Required)

Front Thread:
M34.0 x 0.5 (Male)

Mount:
C-Mount

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
View

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized f/# versions to best suit your instrumentation application needs and to discuss volume requirements, please **contact us**.

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- **Ruggedized (Cr) Designs** Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.

Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series**: Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a **VIS-NIR Broadband Anti-Reflection (BBAR) Coating.**
- Ci Series: Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **Cr Series**: All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.
- **Cx Series**: Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series**: Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 and IPX9K.

Technical Information



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Distortion Plot



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Relative Illumination Plot



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f4



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f4



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f4



#86-594, 6mm, f/4 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f4

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm

Compatible Cameras

;