

[See all 17 Products in Family](#)

TECHSPEC® 700 - 900nm, 12.7mm Dia., Ultrafast Broadband Laser Mirror



Stock #62-765 **20+ In Stock**

⊖ 1 ⊕ ₹16,349

ADD TO CART

Volume Pricing	
Qty 1-4	₹16,349 each
Qty 5-9	₹14,480 each
Qty 10+	₹12,845 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror Type:
 Ti:Sapphire 1st Harmonic Typical Applications:

Physical & Mechanical Properties

Paralleism (arcmin):
 <5

85	Clear Aperture (%) :
Commercial Polish	Back Surface :
12.70 +0.0/-0.2	Diameter (mm) :
6.35 ±0.20	Thickness (mm) :
Optical Properties	
10-5	Surface Quality :
99.7	Reflection at DWL (%) :
R _{avg} >99.7% @ 730 - 870nm R _s >99.7% @ 685 - 935nm	Coating Specification :
0 ±20fs ² @ 700 - 900nm (s-pol) 0 ±20fs ² @ 740 - 860nm (p-pol)	GDD Specification :
700 - 900	Wavelength Range (nm) :
λ/10	Surface Flatness (P-V) :
Dielectric	Coating Type :
Ultrafast (700-900nm)	Coating :
800	Design Wavelength DWL (nm) :
45	Angle of Incidence (°) :
Fused Silica (Corning 7980)	Substrate : <input type="checkbox"/>
10fs ³ @ 800nm, s-pol 40fs ³ @ 800nm, p-pol	TOD Specification :
0.26 J/cm ² @ 800nm, 100fs FWHM, P-Polarization, 1 pulse (typical) 0.23 J/cm ² @ 800nm, 100fs FWHM, 100Hz, P-Polarization, 1000 pulses (typical)	Damage Threshold, By Design : <input type="checkbox"/>
Regulatory Compliance	
Compliant	RoHS 2015 :
Compliant	Reach 205 :
View	Certificate of Conformance :
Lithuania	Country of Origin :
Edmund Optics India Private Limited	Imported By :


Product Details

- Designed with High Reflectivity for Ultrafast Beam Steering
- Ion-Beam Sputtered Coating for Low Scatter and Absorption
- GDD as Low as 0±20fs² at Design Wavelength Range


TECHSPEC® High Performance Low GDD Ultrafast Mirrors are designed to have high reflectivity at 0° or 45° angles of incidence, making them ideal for ultrafast laser beam steering applications. These mirrors have a dispersion compensating coating obtained through a precision ion beam sputtering (IBS) process, providing lower scatter and absorption than traditional dielectric laser mirrors. TECHSPEC High Performance Low GDD Ultrafast Mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. Typical applications include use in the transport of femtosecond laser pulses.

Note: Please [contact us](#) if your application requires a TECHSPEC High Performance Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.


Technical Information




**Ultrafast Ti:Sapphire Laser Mirror
Cubic Term**



**Ultrafast Ti:Sapphire Laser Mirror
Group Velocity Dispersion**



**Ultrafast Ti:Sapphire Laser Mirror
Reflection Curve**



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts