

[See all 12 Products in Family](#)

## 70mm Dia. x 51.5mm FL, Uncoated, Molded Condenser Lens with Smooth Diffuser



Molded Diffuse Aspheric Condenser Lenses

Stock #22-689 **11 In Stock**

- 1 + MRP ₹9,989

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-10	₹9,989 each
Qty 11-49	₹8,980 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**

Maximum of 5 imperfections allowed with an area of 0.8mm, per ISO 10110-7 specification of 5/5 x 0.63. [Click here](#) for more information on the ISO 10110 surface quality specification.

### Physical & Mechanical Properties

Diameter (mm):  
70.00 ±0.20

≤25	<b>Centering (arcmin):</b>
61.20	<b>Clear Aperture CA (mm):</b>
4.00	<b>Edge Thickness ET (mm):</b>
30.68 ±0.50	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
68	<b>Diameter of Asphere (mm):</b>
Plano	<b>Shape of Back Surface:</b>
Smooth	<b>Grit:</b> <input type="checkbox"/>

## Optical Properties

51.50	<b>Effective Focal Length EFL (mm):</b>
0.66	<b>Numerical Aperture NA:</b>
31.80	<b>Back Focal Length BFL (mm):</b>
Tritan	<b>Substrate:</b> <input type="checkbox"/>
±7	<b>Focal Length Tolerance (%):</b>
Uncoated	<b>Coating:</b>
As Mbded	<b>Surface Quality:</b>
0.76	<b>f#:</b>
Plano	<b>Radius R<sub>2</sub> (mm):</b>
350 - 2000	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
587.6	<b>Focal Length Specification Wavelength (nm):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>
Poland	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>





## Product Details

- Combine a Condenser and Diffuser into One Element
- Fine, Medium, and Rough Diffuser Surface Textures
- Provide Diffuse, Homogenous Illumination
- [Condenser Lenses](#) and [Diffusers](#) Also Available

Molded Diffuse Aspheric Condenser Lenses combine a condenser lens and a diffuser into one optical element to simplify illumination systems. These lenses collimate light from LEDs and other light sources to provide homogenous illumination with greater efficiency than using a condenser lens with a ground glass diffuser. Lenses are available with three molded diffuser surface textures (fine, medium, and rough) with coarser textures providing a higher degree of diffusion but lower transmission. Molded Diffuse Aspheric Condenser Lenses feature durable glass substrates, enabling their use with low to high power LEDs, and are ideal for space constrained systems requiring diffuse, homogenous illumination.

## Technical Information

MOLDED DIFFUSE ASPHERIC CONDENSER LENSES

Regular Condenser Lens	Condenser Lens with Smooth Diffuser	Condenser Lens with Medium Diffuser	Condenser Lens with Rough Diffuser
			

Light collimated from an LED using a regular condenser lens and condenser lenses with a diffuser surface. As the texture of the diffuser surface becomes rougher, the level of diffusion increases.

;