

TECHSPEC® 700nm, 25mm Diameter, Low GDD Dichroic Shortpass Ultrafast Filter



TECHSPEC® Low GDD Dichroic Shortpass Ultrafast Filters

Stock #14-002 **1 In Stock**

MRP ₹20,783

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,783 each
Qty 6-25	₹16,647 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter **Type:**

Physical & Mechanical Properties

25.00 **Diameter (mm):**

1.05 ±0.1 **Thickness (mm):**

Dimensional Tolerance (mm):
+0.0/-0.2

Optical Properties

Angle of Incidence (°):
45

Cut-Off Wavelength (nm):
700.00

Substrate:
Fused Silica (Corning 7980)

Coating:
Hard Coated

P-Polarization Transmission (%):
>80

Reflection (%):
>97 Average Polarization

Reflection Wavelength (nm):
725 - 900

S-Polarization Transmission (%):
>80

Surface Quality:
60-40

Transmission (%):
>85 Average Polarization

Transmission Wavelength (nm):
400 - 680

Transmitted Wavefront, RMS:
λ/4

Slope Factor (%):
3.00

Cut-Off Tolerance (%):
±2

S-Polarization Reflection (%):
>95

P-Polarization Reflection (%):
>95

Coating Specification:
Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated

Wavelength Range (nm):
400 - 900

GDD Specification (Transmission):
80 ±30fs² @ 450 - 680nm
120 ±80fs² @ 400 - 680nm

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

Reach 235:
Compliant

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reduced Thickness for Limited GDD
- Broad Transmission and Reflection Ranges
- Ideal for Ultrafast Laser Applications
- Controlled GDD Specification Using [In-House Metrology](#)

TECHSPEC® Low GDD Dichroic Shortpass Ultrafast Filters feature thin substrates and a low group delay dispersion (GDD) coating, making them ideal for use with ultrafast laser sources. Designed for a 45° angle of incidence and covering a range of wavelengths, these spectral filters can be used with Ti:sapphire, Nd:doped, and Yb:doped fiber or glass lasers, as well as with optical parametric oscillators and amplifiers. TECHSPEC Low GDD Dichroic Shortpass Ultrafast Filters are ideal for ultrafast laser applications including multi-photon microscopy, nonlinear fluorescence, and femtosecond stimulated Raman spectroscopy. Please contact us if your application requires an ultrafast optical filter with a custom size or wavelength range.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Compatible Mounts
