

[See all 18 Products in Family](#)

**TECHSPEC® 70mm, 120mm Radius, English Goniometer**



TECHSPEC® Goniometers



Stock #66-532 **6 In Stock**

⊖ 1 ⊕ ₹51,712

**ADD TO CART**

Volume Pricing	
Qty 1-2	₹51,712 each
Qty 3+	₹45,037 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

English **Type:**

5 **Resolution (arcmin):**

**Physical & Mechanical Properties**

**Type of Movement:**

Goniometer	
70 x 70	<b>Stage Size (mm):</b>
±10	<b>Travel (°):</b>
Aluminium Stage	<b>Construction:</b>
0.5	<b>Leadscrew Pitch (mm):</b>
6	<b>Load Capacity (kg):</b>
120	<b>Radius R (mm):</b>
2.75 x 2.75	<b>Stage Size (inches):</b>
0.3	<b>Weight (kg):</b>

## Hardware & Interface Connectivity

Lead Screw	<b>Type of Drive:</b>
------------	-----------------------

## Threading & Mounting

(9) ¼-20, (4) 6-32, (8) 2-56	<b>Mounting Threads:</b>
------------------------------	--------------------------

## Regulatory Compliance

Compliant	<b>RoHS 2015:</b>
View	<b>Certificate of Conformance:</b>
Compliant	<b>REACH 241:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited	<b>Imported By:</b>

## Product Details


70mm and 125mm stages mount directly and do not require bottom adapter plates.

- Metric and English Hole Patterns Available
- Stackable for Two-Axis Rotation
- Mechanically Compatible with our [TECHSPEC® Stages](#)

TECHSPEC® Goniometers allow for precise angular adjustment of an object about a fixed point located above the center of the mounting surface. They provide true tip and tilt adjustment of any optical component and are often used to accurately direct lasers and align mirrors in beam steering applications. These goniometers are available in with Metric and English hole patterns. TECHSPEC® Goniometers are available in different plate sizes to accommodate a host of applications. Each size is offered in several radii of movement for easily stacking into two axis configurations. To provide motion about a common point in two different axes, mount goniometer stages with smaller radii on top of those with larger radii of the same stage size.

Each goniometer stage features precision movement along a dovetail design with a vernier scale for high-resolution measurements and movement repeatability. A locking thumbscrew allows each to be held securely in place. 30mm and 40mm goniometer stages are constructed of durable black painted brass, while 70mm goniometer stages are constructed of black anodized aluminum. [Bottom adapter plates](#), sold separately, are required to mount 30mm and 40mm stages to standard breadboards; 70mm stages will mount directly.

## Technical Information



		Top Stage																													
		30mm Linear Dovetail	30mm Linear	30mm Vertical	30mm Tip/Tilt	30mm Goniometer	30mm Rotary	40mm Linear Dovetail	40mm Linear	40mm Vertical	40mm Tip/Tilt	40mm Goniometer	40mm Rotary	65mm Linear Dovetail	65mm Linear	65mm Vertical	65mm Tip/Tilt	65mm Goniometer	65mm Rotary	70mm Linear Dovetail	70mm Linear	70mm Vertical	70mm Tip/Tilt	70mm Goniometer	70mm Rotary	125mm Linear	125mm Vertical	125mm Tip/Tilt	125mm Rotary		
Bottom Stage	30mm Linear Dovetail																														
	30mm Linear																														
	30mm Vertical																														
	30mm Tip/Tilt																														
	30mm Goniometer																														
	30mm Rotary																														
	40mm Linear Dovetail																														
	40mm Linear																														
	40mm Vertical																														
	40mm Tip/Tilt																														
	40mm Goniometer																														
	40mm Rotary																														
	65mm Linear Dovetail																														
	70mm Linear																														
70mm Vertical																															
70mm Tip/Tilt																															
70mm Goniometer																															
70mm Rotary																															
125mm Linear																															
125mm Vertical																															
125mm Tip/Tilt																															
125mm Rotary																															

