

TECHSPEC® 75 x 100mm Protected Silver, 4-6λ Mirror



Stock **#36-055** 10 TO 12 DAYS

- 1 +

₹5,612.00

ADD TO CART

Qty 1-5
₹5,612.00
Qty 6+
₹5,090.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
75.0 x 100.0

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 71.25 x 95.00
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 100.00
Width (mm): 75.00
Damage Threshold, By Design: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant