

[See all 13 Products in Family](#)

TECHSPEC® 7.16mm Silver and NIR II Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock #12-670 **2 In Stock**

⊖ 1 ⊕ ₹26,640

ADD TO CART

Volume Pricing	
Qty 1-5	₹26,640 each
Qty 6-25	₹21,330 each
Qty 26-49	₹20,070 each
Need More?	Request Quote

Product Downloads

General

Retroreflector **Type:**

Physical & Mechanical Properties

+0.0/-0.1 **Diameter Tolerance (mm):**

7.20	Inner Diameter (mm):
25.40	Outer Diameter (mm):
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25	
Optical Properties	
±10	Beam Deviation (arcsec):
NIR II & Silver with protective overcoat	Coating:
N-BK7	Substrate: □
60-40	Surface Quality:
Left-Handed	Image Orientation:
Coating Specification: Reflective Surfaces: $R_{abs} > 97\%$ FROM 400 - 2500nm @ 0° AOI $R_{avg} > 98\%$ FROM 400 - 2500nm @ 0° AOI Entrance: $R_{abs} \leq 1.5\%$ @ 750 - 800nm, $R_{abs} \leq 1.0\%$ @ 800 - 1550nm, $R_{avg} \leq 0.7\%$ @ 750 - 1550nm	
180	Ray Deviation (°):
750 - 1550	Wavelength Range (nm):
0.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:

Threading & Mounting

(1) 1/4-20, (1) #8	Mounting Threads:
--------------------	--------------------------

Regulatory Compliance


Not Compliant	RoHS 2015:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details


- Incident Light is Reflected Back to the Source
- Useful for Surveying and Alignment
- 1/4-20 Tapped Holes for Easy Mounting
- Also Available [Unmounted](#)

TECHSPEC® Mounted N-BK7 Corner Cube Retroreflectors are mounted in an aluminum body and held in place with RTV potting cement. Due to their complex shape, corner cube retroreflectors can often be challenging to mount. These retroreflectors provide a convenient and durable solution. TECHSPEC® Mounted N-BK7 Corner Cube Retroreflectors are easily integrated via two 1/4-20 tapped holes. In addition, each retroreflector has silvered reflecting surfaces to decrease polarization effects and increase field of view. For dimension details, see the "Technical Information" tab.


Corner cube retroreflectors are designed to reflect any ray or beam entering the prism face, regardless of the prism's orientation, back onto itself. A mirror will only do that at the normal angle of incidence. As a result, corner cube retroreflectors are ideal where precision alignment is difficult or time-consuming.



Technical Information



Stock No.	Inner Diameter ID	Outer Diameter OD	H	X
#49-079	7.16	25.40	7.92	14.27
#45-203	12.7	31.75	11.73	18.08
#12-216	12.7	31.75	11.73	18.08
#12-671	12.7	31.75	11.73	18.08
#45-188	25.4	38.10	20.62	26.98
#12-217	25.4	38.10	20.62	26.98
#12-672	25.4	38.10	20.62	26.98
#45-190	38.1	50.80	31.06	37.41
#45-192	50.8	63.50	39.95	46.30
#49-080	63.5	76.20	49.83	56.18
#49-081	76.2	88.90	58.72	65.07



Units: mm

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).