

[See all 32 Products in Family](#)

# 750 - 900nm (Ti:Sapphire), 2.5-4mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- $\pi$ Shaper\_TiS\_Q-3

See More by [AdiOptica](#)



Stock #25-927 **1 In Stock**

1  MRP ₹3,35,516

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹3,35,516 each
Qty 5+	₹2,98,237 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Focal- $\pi$ Shaper\_TiS\_Q-3 **Model Number:**

Beam Shaper **Type:**

**Physical & Mechanical Properties**

Length (mm):

29.00

Weight (g):

50

Clear Aperture CA (mm):

20

Diameter (mm):

42.00

Input Beam Diameter,  $1/e^2$  (mm):

8 - 12

**Optical Properties**

Transmission (%):

&gt;99

Design Wavelength DWL (nm):

750, 900

Wavelength Range (nm):

750 - 900

Input Beam Mode:

TEM<sub>00</sub>Typical Input Beam Mode Quality,  $M^2$ :

&lt;1.5

Input Beam Divergence (mrad):

±20

**Electrical**

Maximum Input Power, CW (kW):

0.1

**Threading & Mounting**

Inner Thread:

M30 x 0.75

Outer Thread:

M30 x 0.75

**Regulatory Compliance**

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 250:

[Compliant](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

**Product Details**

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

**Technical Information**

