

[See all 13 Products in Family](#)

75 x 75mm, 0.7mm Thick, EAGLE XG® Window



EAGLE XG® Windows

Stock **#29-370** [CONTACT US](#)

- 1 + MRP ₹4,565

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹4,565 each
Qty 6-25	₹3,632 each
Qty 26-49	₹3,430 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Glass **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

67.50 x 67.50	
75 x 75 ±0.25	Dimensions (mm):
0.70 ±0.07	Thickness (mm):
75.00	Length (mm):
75.00	Width (mm):
Protective as needed	Bevel:
90	Clear Aperture (%):
Scribe Cut and Seamed	Edges:
0.23	Poisson's Ratio:
73.6	Young's Modulus (GPa):

Optical Properties

Uncoated	Coating:
EAGLE XG®	Substrate: <input type="checkbox"/>
1.51	Index of Refraction (n_d):
80-50	Surface Quality:
350 - 2000	Wavelength Range (nm):

Material Properties

2.38	Density (g/cm³):
3.17 (0 to +300°C)	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Thin 0.7mm EAGLE XG® Substrates
- High Chemical Resistance and Excellent Durability
- Low Density for Weight Sensitive Applications

EAGLE XG® Windows are constructed from heavy-metal free glass through a fusion drawn process, providing these windows with exceptionally smooth, flat surfaces. These windows have high transmission in the visible spectrum, excellent environmental durability, and high chemical resistance. The low density of Corning® EAGLE XG® coupled with the thinness of these windows makes them ideal for weight and space sensitive applications. EAGLE XG® Windows are used as substrates for mobile device LCDs, substrates for polarizers, wafers for semiconductor applications, or protective windows for electronic displays.

Technical Information



Quote Your Size
