

TECHSPEC[®] 75mm Dia., 0.63 Numerical Aperture NIR Coated, Aspheric Lens



Stock #22-716 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹69,600.00

ADD TO CART

Qty 1-5
₹69,600.00
Qty 6+
₹55,680.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.1

Effective Focal Length EFL (mm):
60.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 45.77
Substrate: N-SF5
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 67.5
Edge Thickness ET (mm): 4.73
Center Thickness CT (mm): 23.80 ±0.1
f#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 16.67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant