

TECHSPEC® 75mm Dia. x 400mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-419** 10 TO 12 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

₹26,100.00

ADD TO CART

Qty 1-5

₹26,100.00

Qty 6+

₹20,880.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
75.00 +0.0/-0.025

Effective Focal Length EFL (mm):

400.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 392.10
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 73.50
Centering (arcmin): <1
Center Thickness CT (mm): 17.05 ±0.20
Center Thickness CT 1 (mm): 11.05 ±0.10
Center Thickness CT 2 (mm): 6.00 ±0.10
Radius R ₁ (mm): 246.50
Radius R ₂ (mm): -180.92
Radius R ₃ (mm): -526.70
Edge Thickness ET (mm): 12.84
Substrate: N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 5.33
Numerical Aperture NA: 0.09
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View