

## 7.5mm Dia. x 6.6mm FL, Aspheric Condenser Lens



Stock **#19-509** 10 TO 12 DAYS  
[Other Coating Options](#)

- 1 + **₹2,958.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| ₹2,958.00                     |
| Qty 11+                       |
| ₹2,697.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Diameter (mm):  
7.50 +0.0/-0.2

Effective Focal Length EFL (mm):  
6.60

Numerical Aperture NA:  
0.57

Back Focal Length BFL (mm):

|                                                |
|------------------------------------------------|
| 4.3                                            |
| <b>Substrate:</b> <div>H-K51</div>             |
| <b>Focal Length Tolerance (%)</b> :<br>±5      |
| <b>Coating:</b><br>Uncoated                    |
| <b>Centering (arcmin):</b><br>≤30              |
| <b>Surface Quality:</b><br>80-50 (typical)     |
| <b>Clear Aperture CA (mm):</b><br>6.75         |
| <b>Edge Thickness ET (mm):</b><br>1.18         |
| <b>Center Thickness CT (mm):</b><br>3.50 ±0.30 |
| <b>f/#:</b><br>0.88                            |
| <b>Bevel:</b><br>Protective bevel as needed    |
| <b>Diameter of Asphere (mm):</b><br>7.5        |
| <b>Radius R<sub>2</sub> (mm):</b><br>∞         |
| <b>Shape of Back Surface:</b><br>Plano         |
| <b>Type:</b><br>Condenser Lens                 |
| <b>Wavelength Range (nm):</b><br>350 - 2000    |
| <b>Conjugate Distance:</b><br>Infinite         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |