

TECHSPEC<sup>®</sup> 75mm Sq., 4mm Thick, YAG-BBAR Coated, λ/4 N-BK7 Window



Stock #15-798 10 TO 12 DAYS

-

1

+

₹17,400.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹17,400.00                    |
| Qty 6+                        |
| ₹13,920.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Abbe Number (v<sub>d</sub>):  
64.17

Bevel:  
Protective as needed

Clear Aperture (%):  
90

Clear Aperture CA (mm):

|                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------|
| 67.50 x 67.50                                                                                                                                 |
| <b>Dimensions (mm):</b><br>75.00 x 75.00                                                                                                      |
| <b>Thickness (mm):</b><br>4.00 ±0.20                                                                                                          |
| <b>Coating:</b><br>YAG-BBAR (500-1100nm)                                                                                                      |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C)                                |
| <b>Density (g/cm³):</b><br>2.51                                                                                                               |
| <b>Edges:</b><br>Fine Ground                                                                                                                  |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.516                                                                                            |
| <b>Knoop Hardness (kg/mm²):</b><br>610                                                                                                        |
| <b>Parallelism (arcmin):</b><br><1                                                                                                            |
| <b>Poisson's Ratio:</b><br>0.206                                                                                                              |
| <b>Substrate:</b><br><a href="#">N-BK7</a>                                                                                                    |
| <b>Surface Flatness (P-V):</b><br>λ/4                                                                                                         |
| <b>Surface Quality:</b><br>60-40                                                                                                              |
| <b>Type:</b><br>Protective Window                                                                                                             |
| <b>Wavelength Range (nm):</b><br>500 - 1100                                                                                                   |
| <b>Young's Modulus (GPa):</b><br>82                                                                                                           |
| <b>Length (mm):</b><br>75.00                                                                                                                  |
| <b>Width (mm):</b><br>75.00                                                                                                                   |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns                                                         |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |