

TECHSPEC[®] 76.2 x 178.5mm EFL 45° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-588** **2 In Stock**
[Other Coating Options](#)

-

1

+

₹57,220

ADD TO CART

Volume Pricing	
Qty 1-5	₹57,220 each
Qty 6-25	₹51,381 each
Qty 26-50	₹45,659 each
Need More?	Request Quote

Product Downloads

General	
Off-Axis Parabolic Mirror	Type:
Physical & Mechanical Properties	
126.26	Y Offset (mm):
76.20 +0.00/-0.38	Diameter (mm):


90	Clear Aperture (%):
<100 RMS	Surface Roughness (□):
Optical Properties	
Metal	Coating Type:
Protected Aluminum (400-2000nm)	Coating:
45	Off-Set Angle (°):
400 - 2000	Wavelength Range (nm):
178.53	Effective Focal Length EFL (mm):
Aluminum 6061-T6	Substrate: □
Ravg ≥85% @400 - 700nm Ravg ≥97% @2,000 - 12,000nm	Coating Specification:
±1	Focal Length Tolerance (%):
152.4	Parent Focal Length PFL (mm):
3/4λ	Surface Figure, RMS:
80-50	Surface Quality:
304.80	Radius of Curvature (mm):
3/2λ	Reflected Wavefront, RMS:
Threading & Mounting	
#63-375	Compatible Mounting Plates:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Aluminum Coatings for UV, Visible, and NIR Applications
- Range of Surface Roughness, Including 50Å and 100Å
- 15°, 30°, 45°, 60°, or 90° Offset Angle Options
- Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Aluminum Off-Axis Parabolic Mirrors (OAPs) are a cost-effective solution for focusing incident light with minimal scatter loss. Available with enhanced or protected aluminum coatings, these OAP mirrors offer high reflectivity from the ultraviolet (UV) to the near infrared (NIR). These Aluminum OAPs are manufactured with multiple surface roughness specifications, offering designers the choice between high performance, low scatter mirrors and more cost sensitive options. TECHSPEC® Aluminum Off-Axis Parabolic Mirrors are used in optical systems such as Schlieren and spectroscopy systems, as well as in laser systems to focus laser beams. For increased system integration flexibility, mounting plates that thread to the base of these off-axis parabolic mirrors are available.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).