

TECHSPEC[®] 76.2mm Dia. 1030nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC[®] Yb:YAG Laser Line Mirrors



Stock **#27-036** 7 In Stock

-

1

+

₹57,375

ADD TO CART

Volume Pricing	
Qty 1-5	₹57,375 each
Qty 6-25	₹51,692 each
Qty 26-49	₹45,932 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Laser Mirror	
Physical & Mechanical Properties	
Parallelism (arcmin):	<3
Clear Aperture (%):	90
Back Surface:	Commercial Polish
Diameter (mm):	76.20 +0.00/-0.10
Thickness (mm):	12.70 ±0.20
Optical Properties	
Surface Quality:	10-5
Reflection at DWL (%):	99.8
Coating Specification:	R _{abs} >99.8% @ 1030nm
Wavelength Range (nm):	1020 - 1040
Surface Flatness (P-V):	λ/10
Coating Type:	Dielectric
Coating:	Laser Mirror (1030nm)
Design Wavelength DWL (nm):	1030
Angle of Incidence (°):	0-45
Substrate:	Fused Silica (Corning 7980)
Damage Threshold, By Design:	15 J/cm² @ 1030nm, 20ns, 20Hz
Regulatory Compliance	
RoHS 2015:	Compliant
Reach 209:	Compliant
Certificate of Conformance:	View

PRODUCT DETAILS

- >99.8% Reflectivity at Yb:YAG Harmonic Frequencies
- Guaranteed High Laser Damage Thresholds
- 10-5 Surface Quality for Reduced Scatter in Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Yb:YAG Laser Line Mirrors are designed to meet the demanding requirements of Ytterbium doped fiber (Yb:doped fiber) and thin-disk laser systems. These mirrors feature laser grade substrates with λ/10 surface flatness and 10-5 surface quality to minimize scattering effects. The durable dielectric coatings are designed for high reflectivity at their design wavelengths as well as high damage thresholds at both continuous wave and pulsed laser operating conditions. TECHSPEC Yb:YAG Laser Line Mirrors are ideal for laser applications that include laser ablation, welding, drilling, cutting, and sintering. Dielectric Yb:YAG mirror coatings for applications which require 343nm, 515nm, and 1030nm are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).