

TECHSPEC® 76.2mm Dia., 12.7mm Thick, 1064nm, λ/10 Fused Silica Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#20-450** 10 TO 12 DAYS

⊖ 1 ⊕ **₹68,295.00**

ADD TO CART

Qty 1-5
₹68,295.00
Qty 6+
₹54,636.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
68.58

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm): 1064
Diameter (mm): 76.20 +0.00/-0.10
Substrate: Fused Silica (Corning 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 12.70 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Coating Specification: R_{abs} <0.25% @ 1064nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz
Fused Silica Grade: 7980 0A
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View