

TECHSPEC<sup>®</sup> 785nm, 25mm Diameter, Raman Edge Filter



Stock **#86-245** 1 In Stock

-

1

+

₹56,831

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹56,831 each                  |
| Qty 10+        | ₹47,333 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                           |
|----------------------------------|---------------------------|
| Longpass Filter                  | Type:                     |
| Bandwidth (nm): >700             | Note:                     |
| Physical & Mechanical Properties |                           |
| 25.00 +0.0/-0.1                  | Diameter (mm):            |
| ±0.1                             | Thickness Tolerance (mm): |

|                                                                             |                                 |
|-----------------------------------------------------------------------------|---------------------------------|
| >80                                                                         | Clear Aperture (%):             |
| Optical Properties                                                          |                                 |
| 0 ±2                                                                        | Angle of Incidence (°):         |
| ≥6.0                                                                        | Optical Density OD (Average):   |
| 792.80                                                                      | Cut-On Wavelength (nm):         |
| 785                                                                         | Design Wavelength DWL (nm):     |
| Fused Silica (Coming 7980)                                                  | Substrate: □                    |
| Hard Coated                                                                 | Coating:                        |
| 60-40                                                                       | Surface Quality:                |
| >90                                                                         | Transmission (%):               |
| <7.8                                                                        | Transition Width (nm):          |
| <λ/4 @ 633nm                                                                | Transmitted Wavefront, RMS:     |
| T <sub>abs</sub> ≥93% @ 804 - 900nm<br>T <sub>avg</sub> ≥90% @ 804 - 1500nm | Coating Specification:          |
| 785 - 1500                                                                  | Wavelength Range (nm):          |
| 785.00                                                                      | Laser Blocking Wavelength (nm): |
| Threading & Mounting                                                        |                                 |
| 3.5                                                                         | Mount Thickness (mm):           |
| Environmental & Durability Factors                                          |                                 |
| Environmental: ML-STD-810F<br>Physical: ML-C-48497A                         | Durability:                     |
| Regulatory Compliance                                                       |                                 |
| Compliant                                                                   | RoHS 2015:                      |
| Compliant                                                                   | Reach 209:                      |
| View                                                                        | Certificate of Conformance:     |
| United States                                                               | Country of Origin:              |
| Edmund Optics India Private Limited                                         | Imported By:                    |

## Product Details

- High Transmission for Detecting Weak Signals
  - Deep Blocking for Maximum Laser Rejection
  - Ideal for Raman Spectroscopy or Life Science Instrumentation
- TECHSPEC® Raman Longpass Edge Filters are single filter solutions for reducing spectral noise in Stokes shift applications. These filters are designed to create sharp transitions between transmitted Raman signals and blocked laser wavelengths. Designed to detect even the smallest Raman shifts, TECHSPEC Raman Longpass Edge Filters are ideal for integration into Raman spectroscopy or confocal microscopy systems. The hard coated design offers superior transmission characteristics than comparable traditional coated filters.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

;