

[See all 45 Products in Family](#)

785nm 50mW Pigtailed Laser Diode



Stock #23-785 **1 In Stock**

- 1 + MRP ₹1,65,672

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹1,65,672 each
Qty 10+	₹1,49,105 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Type of Laser:
Diode

Laser Class - CDRH:
IIIb

Physical & Mechanical Properties

Length of Fiber (m):

Optical Properties

0.12 Numerical Aperture NA:

Fiber-Coupled Spatial Mode:

5 Fiber Diameter (μm):

785.00 \pm 10 Wavelength (nm):

Red Color:

Electrical

50 Output Power (mW):

Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Power Supply Required and Sold Separately.
USA: [#73-818](#)
Europe: [#73-818](#)
Japan: [#13-640](#)
Korea: [#33-770](#)
China: [#73-818](#)

FC/PC Connector:

Environmental & Durability Factors

+15 to +30 Operating Temperature ($^{\circ}\text{C}$):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

China Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Single Mode Fiber with FC/PC Connector
- 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
- Integrated Driver for Easy Operation

Pigtailed Laser Diode Modules feature an integrated 1m long, single mode fiber with an FC/PC connector. These laser diodes also feature an integrated driver for plug and play operation, only requiring a 5V external power supply ([#73-818](#)). Pigtailed Laser Diode Modules are available with VIS and NIR wavelengths ranging from 405 to 1550nm, with output powers ranging from 1 to 100mW. Their plug and play operation make these laser diodes ideal for a wide range of laboratory and OEM applications.